



GT654

Hydro Reinforced Water Activated Gum Tape

Hydro Reinforced Water Activated Gum Tape	
Color	Natural Kraft / Bleached White
Top Ply	23 lbs (37 g/m ²)
Bottom Ply	23 lbs (37 g/m ²)
Laminate	Non-Asphaltic Polypropylene based polymer; complies with FDA CFR 175.105
Adhesive	High tack, water-activated, modified cornstarch based
MD Reinforcement	110 Denier Fiberglass (1-1-1-1-1; in 72mm)
CS Reinforcement	150 Denier Fiberglass – Diamond Pattern 1” spacing, 45 degree angle
Caliper	5.9 mils (150 micron)
MD Tensile	55 lbs/in (245N/25mm)
CD Tensile	24 lbs/in (108N/25mm)
Storage Conditions	Store in a clean, dry place at room temperature. Avoid temperature and humidity extremes.
<p>Important Notice: The above listed information is based on calculations and tests we believe to be reliable. However, the accuracy and completeness are not guaranteed. Before using, user shall determine the suitability of the product for its own use and assumes all risk and liability related to the product. The seller limits its obligations to replacement or at its option, reimbursement of the purchase price of products shown to the seller's satisfaction to have been defective at the time the seller sold it.</p>	